



**NO TOOLS NECESSARY WHEN MOUNTING MICROPHONES OR CAPSULES.**

**1) Telinga Modular MONO FOAM (INCLUDED)**

Compatible with most omnidirectional pencil style mics (length not exceeding 180 mm & diameter max. 24 mm) **forward** in the dish. For omni or cardioid mics **facing** the dish we suggest maximum length 80 mm / diameter max 24 mm. Longer models of mics may also be possible to use facing the dish without the Rycote Telinga Basket front cap attached.

**2) Telinga Modular STEREO FOAM with preinstalled plate/baffle (INCLUDED)**

Allows smaller omni mics, lavaliers or electret capsules (max 25 mm) to be mounted side by side of the plate in respective foam channel in PZM configuration.

**Please note:** The Telinga Modular is not compatible with Telinga stereo or Twin Science parabolic mics.

**If you ask us?** We love Schoeps mics (mono) & Primo electret capsules (for stereo PZM arrangements). The complete assembling of the Telinga Modular is done within minutes without the need of any tools. The Telinga Modular is highly resistant to rain, humidity and wind. Please note that Tripod Stand or Tripod Mount is not included (sold separately).

**Please note!** Telinga Modular foams are interchangeable **without glue** so you never have to send a Telinga Modular foam back for replacement.